

## Precautionary statements - General

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P103	Read label before use

## Precautionary statements — Prevention

P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P210	Keep away from heat/sparks/open flames/hot surfaces. — No smoking.
P211	Do not spray on an open flame or other ignition source.
P220	Keep/Store away from clothing/.../combustible materials.
P221	Take any precaution to avoid mixing with combustibles/...
P222	Do not allow contact with air.
P223	Keep away from any possible contact with water, because of violent reaction and possible flash fire.
P230	Keep wetted with ...
P231	Handle under inert gas.
P232	Protect from moisture.
P233	Keep container tightly closed.
P234	Keep only in original container.
P235	Keep cool.
P240	Ground/bond container and receiving equipment.
P241	Use explosion-proof electrical/ventilating/lighting/.../equipment.
P242	Use only non-sparking tools.
P243	Take precautionary measures against static discharge.
P244	Keep reduction valves free from grease and oil.
P251	Do not subject to grinding/shock/.../friction.
P251	Pressurized container: Do not pierce or burn, even after use.
P260	Do not breathe dust/fume/gas/mist/vapours/spray.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P262	Do not get in eyes, on skin, or on clothing.
P263	Avoid contact during pregnancy/while nursing.
P264	Wash hands thoroughly after handling.
P264	Wash skin thoroughly after handling.
P270	Do not eat, drink or smoke when using this product.
P271	Use only outdoors or in a well-ventilated area.
P272	Contaminated work clothing should not be allowed out of the workplace.
P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P281	Use personal protective equipment as required.
P282	Wear cold insulating gloves/face shield/eye protection.
P283	Wear fire/flame resistant/retardant clothing.
P284	Wear respiratory protection.
P285	In case of inadequate ventilation wear respiratory protection.
P231 + P232	Handle under inert gas. Protect from moisture.
P235 + P410	Keep cool. Protect from sunlight.

## Precautionary statements — Response

P301	IF SWALLOWED:
P304	IF INHALED:
P305	IF IN EYES:
P306	IF ON CLOTHING:
P307	IF exposed:
P308	IF exposed or concerned:
P309	IF exposed or if you feel unwell:
P310	Immediately call a POISON CENTER or doctor/physician.
P311	Call a POISON CENTER or doctor/physician.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P313	Get medical advice/attention.
P314	Get medical advice/attention if you feel unwell.
P315	Get immediate medical advice/attention.

<b>P320</b>	Specific treatment is urgent (see ... on this label).
<b>P321</b>	Specific treatment (see ... on this label).
<b>P322</b>	Specific measures (see ... on this label).
<b>P330</b>	Rinse mouth.
<b>P331</b>	Do NOT induce vomiting.
<b>P332</b>	IF SKIN irritation occurs:
<b>P333</b>	If skin irritation or rash occurs:
<b>P334</b>	Immerse in cool water/wrap in wet bandages.
<b>P335</b>	Brush off loose particles from skin.
<b>P336</b>	Thaw frosted parts with lukewarm water. Do not rub affected area.
<b>P337</b>	If eye irritation persists:
<b>P338</b>	Remove contact lenses, if present and easy to do. Continue rinsing.
<b>P340</b>	Remove victim to fresh air and keep at rest in a position comfortable for breathing.
<b>P341</b>	If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.
<b>P342</b>	If experiencing respiratory symptoms:
<b>P350</b>	Gently wash with plenty of soap and water.
<b>P351</b>	Rinse cautiously with water for several minutes.
<b>P352</b>	Wash with plenty of soap and water.
<b>P353</b>	Rinse skin with water/shower.
<b>P360</b>	Rinse immediately contaminated clothing and skin with plenty of water before removing clothes.
<b>P361</b>	Remove/Take off immediately all contaminated clothing.
<b>P362</b>	Take off contaminated clothing and wash before reuse.
<b>P363</b>	Wash contaminated clothing before reuse.
<b>P370</b>	In case of fire:
<b>P371</b>	In case of major fire and large quantities:
<b>P372</b>	Explosion risk in case of fire.
<b>P373</b>	DO NOT fight fire when fire reaches explosives.
<b>P374</b>	Fight fire with normal precautions from a reasonable distance.
<b>P376</b>	Stop leak if safe to do so. Oxidising gases (section 2.4) 1
<b>P377</b>	Leaking gas fire: Do not extinguish, unless leak can be stopped safely.
<b>P378</b>	Use ... for extinction.
<b>P380</b>	Evacuate area.
<b>P381</b>	Eliminate all ignition sources if safe to do so.
<b>P390</b>	Absorb spillage to prevent material damage.
<b>P391</b>	Collect spillage. Hazardous to the aquatic environment
<b>P301 + P310</b>	IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.
<b>P301 + P312</b>	IF SWALLOWED: call a POISON CENTER or doctor/physician IF you feel unwell.
<b>P301 + P330 + P331</b>	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
<b>P302 + P334</b>	IF ON SKIN: Immerse in cool water/wrap in wet bandages.
<b>P302 + P350</b>	IF ON SKIN: Gently wash with plenty of soap and water.
<b>P302 + P352</b>	IF ON SKIN: wash with plenty of soap and water.
<b>P303 + P361 + P353</b>	IF ON SKIN (or hair): Remove/Take off Immediately all contaminated clothing. Rinse SKIN with water/shower.
<b>P304 + P312</b>	IF INHALED: Call a POISON CENTER or doctor/physician if you feel unwell.
<b>P304 + P340</b>	IF INHALED: Remove victim to fresh air and Keep at rest in a position comfortable for breathing.
<b>P304 + P341</b>	IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.
<b>P305 + P351 + P338</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
<b>P306 + P360</b>	IF ON CLOTHING: Rinse Immediately contaminated CLOTHING and SKIN with plenty of water before removing clothes.
<b>P307 + P311</b>	IF exposed: call a POISON CENTER or doctor/physician.
<b>P308 + P313</b>	IF exposed or concerned: Get medical advice/attention.
<b>P309 + P311</b>	IF exposed or if you feel unwell: call a POISON CENTER or doctor/physician.
<b>P332 + P313</b>	IF SKIN irritation occurs: Get medical advice/attention.
<b>P333 + P313</b>	IF SKIN irritation or rash occurs: Get medical advice/attention.
<b>P335 + P334</b>	Brush off loose particles from skin. Immerse in cool water/wrap in wet bandages.
<b>P337 + P313</b>	IF eye irritation persists: Get medical advice/attention.
<b>P342 + P311</b>	IF experiencing respiratory symptoms: call a POISON CENTER or doctor/physician.
<b>P370 + P376</b>	in case of fire: Stop leak if safe to Do so.
<b>P370 + P378</b>	In case of fire: Use ... for extinction.
<b>P370 + P380</b>	in case of fire: Evacuate area.
<b>P370 + P380 + P375</b>	in case of fire: Evacuate area. Fight fire remotely due to the risk of explosion.
<b>P371 + P380 + P375</b>	in case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion.

#### Precautionary statements — Storage

<b>P401</b>	Store ...
<b>P402</b>	Store in a dry place.
<b>P403</b>	Store in a well-ventilated place.
<b>P404</b>	Store in a closed container.

<b>P405</b>	Store locked up.
<b>P406</b>	Store in corrosive resistant/... container with a resistant inner liner.
<b>P407</b>	Maintain air gap between stacks/pallets.
<b>P410</b>	Protect from sunlight.
<b>P411</b>	Store at temperatures not exceeding ... oC/...oF.
<b>P412</b>	Do not expose to temperatures exceeding 50 oC/ 122 oF.
<b>P413</b>	Store bulk masses greater than ... kg/...lbs at temperatures not exceeding ... oC/...oF.
<b>P420</b>	Store away from other materials.
<b>P422</b>	Store contents under ...
<b>P402 + P404</b>	Store in a dry place. Store in a closed container.
<b>P403 + P233</b>	Store in a well-ventilated place. Keep container tightly closed.
<b>P403 + P235</b>	Store in a well-ventilated place. Keep cool.
<b>P410 + P403</b>	Protect from sunlight. Store in a well-ventilated place.
<b>P410 + P412</b>	Protect from sunlight. Do not expose to temperatures exceeding 50 oC/122oF.
<b>P411 + P235</b>	Store at temperatures not exceeding ... oC/...oF. Keep cool.

**Precautionary statements — Disposal**

<b>P501</b>	Dispose of contents/container to.....
<b>P502</b>	Refer to manufacturer/supplier for information on recovery/recycling