

# Material Safety Data Sheet

OSHA "Hazard Communication" (29 CFR 1910.1200)

## Hanks' Balanced Salt Solution

HBSS Modified, with calcium, with magnesium, without phenol red

CATALOG NO. 55037

### Section I – Product Identification

**Product Name:**

Hanks' Balanced Salt Solution, HBSS Modified, with calcium, with magnesium, without phenol red

**Product Number:**

55037

**Product Classification:**

Cell Culture Reagent

### Section II – Physical Data

**Appearance:**

Clear colorless solution

**pH:**

7.0 - 7.4

### Section III – Hazardous Ingredients

Section Not Applicable.

### Section IV – First Aid

In case of contact with eyes, flush thoroughly with water and contact a physician. In case of accidental swallowing, rinse the mouth with fresh water, provided the person is conscious. Contact a physician. In case of contact with skin, wash the affected area with copious quantities of soap and water. Should irritation occur, contact a physician. In case of inhalation, remove to fresh air. Give oxygen if breathing becomes difficult. If not breathing, give artificial respiration. Contact a physician.

### Section V – Fire and Explosion Hazard Data

**Extinguishing Media:**

Water spray, dry chemical powder or appropriate foam. Toxic fumes may be released upon combustion.

### Section VI – Health (Toxicological) Hazard Data

This product is a potential irritant to eyes, respiratory system and skin. The product may also be harmful if ingested. Complete toxicological properties have yet to be determined.

### Section VII – Stability and Reactivity

Stable. Hazardous Polymerization will not occur.

---

#### United States

SAFC Biosciences, Inc.  
13804 W. 107th Street  
Lenexa, Kansas 66215  
USA  
Phone +1 913-469-5580  
Toll free-USA 1 800-255-6032  
Fax +1 913-469-5584  
E-mail info-na@sial.com

#### Europe

SAFC Biosciences Ltd.  
Smeaton Road, West Portway  
Andover, Hampshire SP10 3LF  
UNITED KINGDOM  
Phone +44 (0)1264-333311  
Fax +44 (0)1264-332412  
E-mail info-eu@sial.com

#### Asia Pacific

SAFC Biosciences Pty. Ltd.  
18-20 Export Drive  
Brooklyn, Victoria 3025  
AUSTRALIA  
Phone +61 (0)3-9362-4500  
Toll free-AUS 1 800-200-404  
Fax +61 (0)3-9315-1656  
E-mail info-ap@sial.com

## Section VIII – Special Protection Information

### Eye Protection:

Safety glasses or goggles.

### Protective Gloves:

Chemical-resistant gloves.

### Respiratory Protection:

Protective mask recommended.

### Ventilation:

Mechanical (general) or local exhaust

### Other Protection Equipment:

Safety shower and eye bath.

## Section IX – Handling and Storage Precautions/Comments

### Store at:

15 to 30 C. Protect from light.

### Intended Use:

For further manufacturing use. THIS PRODUCT IS NOT INTENDED FOR HUMAN OR THERAPEUTIC USE.

## Section X – Spill or Leak Procedures

### Spill:

Wear respirator, safety goggles and chemical-resistant gloves. Absorb on sand, vermiculite or other absorbent material. Place in a closed container and hold for waste disposal. Wash and ventilate area thoroughly after clean up is complete.

### Waste Disposal:

Follow all Federal, State and Local regulations for chemical waste disposal.

## Section XI – Disclaimer

The information, data and recommendations contained herein are believed to be accurate but may not be all-inclusive and should only be used as a guide. SAFC Biosciences makes no warranty of any kind whatsoever with respect thereto and disclaims all liability from reliance thereon. We reserve the right to revise this MSDS periodically as new information becomes available.

#### Warranty, Limitation of Remedies

SAFC Biosciences warrants to the purchaser for a period of one year from date of delivery that this product conforms to its specifications. Other terms and conditions of this warranty are contained in SAFC Biosciences' written warranty, a copy of which is available upon request. ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. In no case will SAFC Biosciences be liable for any special, incidental, or consequential damages arising out of this product or the use of this product by the customer or any third party based upon breach of warranty, breach of contract, negligence, strict tort, or any other legal theory. SAFC Biosciences expressly disclaims any warranty against claims by any third party by way of infringement or the like. THIS PRODUCT IS INTENDED FOR PURPOSES DESCRIBED ONLY AND IS NOT INTENDED FOR ANY HUMAN OR THERAPEUTIC USE.

Additional Terms and Conditions are contained in the product Catalog, a copy of which is available upon request.

© 2006 SAFC Biosciences, Inc.

Issued April 2006 M55037  
0500 0905 1005

#### United States

SAFC Biosciences, Inc.  
13804 W. 107th Street  
Lenexa, Kansas 66215  
USA  
Phone +1 913-469-5580  
Toll free-USA 1 800-255-6032  
Fax +1 913-469-5584  
E-mail info-na@sial.com

#### Europe

SAFC Biosciences Ltd.  
Smeaton Road, West Portway  
Andover, Hampshire SP10 3LF  
UNITED KINGDOM  
Phone +44 (0)1264-333311  
Fax +44 (0)1264-332412  
E-mail info-eu@sial.com

#### Asia Pacific

SAFC Biosciences Pty. Ltd.  
18-20 Export Drive  
Brooklyn, Victoria 3025  
AUSTRALIA  
Phone +61 (0)3-9362-4500  
Toll free-AUS 1 800-200-404  
Fax +61 (0)3-9315-1656  
E-mail info-ap@sial.com