

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

EX-CELL® CD CHO Fusion – Animal-component free, without L-glutamine, without hypoxanthine, without thymidine, liquid, sterile-filtered, suitable for cell culture

Product Number: 14365C

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Turbidity)	Clear
Appearance (Form)	Solution
Free of ppt	
Appearance (Color)	Report Only (Color)
pH	7.1 - 7.7
Osmolality	292 - 322 mOs/kg
Sterility by USP guidelines	No Microbial Growth Detected
Endotoxin Level	≤ 1.0 EU/ml
Cell Culture Test	≥ 2000000
CD > /= 2.0 X 10E6 cells/mL	
% Viability	≥ 95 %
Cell Line	CHO-K1 Cell Line

Remarks:

Date of manufacture (DDMMYY):

Specification: PRD.0.ZQ5.10000100729

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.