

# NovaSeptum® GO Pre-loaded Disposable Magazine

## Product Description

The NovaSeptum® GO pre-loaded disposable magazine is available with various standard configurations using NovaSeptum® GO high purity bags, bottles, transfer tubes or accurate volume (AV) units. Other configurations are available upon request. For an optimal aseptic solution, use the NovaSeptum® GO pre-loaded disposable magazine together with a 1.5 in. or 2 in. NovAseptic® connector and NovaSeptum® GO pre-loaded starter kit (5/9 shot stainless steel base).



NovaSeptum® GO pre-loaded 1.5 inch single-use magazine

## Specifications

### NovaSeptum® GO Single-Use Magazine, TC 1.5 in./ 2 in., 2 mm

Magazine	30% GF Polysulfone
Locking ring	Polysulfone
First actuation locking tag	Polyamide
<b>Environmental</b>	
Design Temperature, TC holder	Steam in place cycle at up to 145°C (293°F) or Autoclave during 1 hour at up to 134°C (273°F) (when applicable).
Traceability	The product and packaging label includes the catalogue number, lot number and expiration date.
Sterilization	Gamma irradiation between 25 kGy and 40 kGy or Beta irradiation between 25 kGy and 70 kGy.
Component Material Toxicity	All wetted component materials meet the criteria for Class VI testing based on USP <88> Biological Reactivity, <i>in vivo</i> .
Endotoxin level	< 2.15 EU/device for all wetted components.
Assembly	This product is manufactured in a clean room environment complying with class 8 according to ISO® 14644-1.
Packaging	Each single-use pre-loaded holder is double packed.

## Ordering Information

Sampling Type	Sample Volume (mL)	Sample Unit/ Single Use Holder	Qty/pack	Catalogue No.
NovaSeptum® GO AV Accurate Volume Sampling Unit	5	5 Single Sampling Unit	6	E5SU461-90005
	20	5 Single Sampling Unit	4	E5SU461-90020
	50	5 Single Sampling Unit	8	E5SU711-10050
NovaSeptum® GO High Purity Sampling Unit	100	5 Single Sampling Unit	8	E5SU711-10100
	250	5 Single Sampling Unit	7	E5SU711-10250
	1000	5 Single Sampling Unit	6	E5SU711-11000
NovaSeptum® GO Bottle Sampling Unit	60	5 Single Sampling Unit	6	E5SU871-80060
	125	5 Single Sampling Unit	4	E5SU871-80125
	250	5 Single Sampling Unit	3	E5SU871-80250
	500	5 Single Sampling Unit	2	E5SU871-80500

Sampling Type	Sample Volume (mL)	Sample Unit/ Single Use Holder	Qty/pack	Catalogue No.
NovaSeptum® GO AV Accurate Volume Sampling Unit	5	9 Single Sampling Unit	3	E9SU461-90005
	20	9 Single Sampling Unit	2	E9SU461-90020
	50	9 Single Sampling Unit	3	E9SU711-10050
NovaSeptum® GO High Purity Sampling Unit	100	9 Single Sampling Unit	3	E9SU711-10100
	250	9 Single Sampling Unit	3	E9SU711-10250
	1000	9 Single Sampling Unit	3	E9SU711-11000
NovaSeptum® GO Bottle Sampling Unit	60	9 Single Sampling Unit	3	E9SU871-80060
	125	9 Single Sampling Unit	2	E9SU871-80125
	250	9 Single Sampling Unit	1	E9SU871-80250

## NovaSeptum® GO Pre-loaded Starter Kits

Device Description	Qty/pack	Catalogue No.
NovaSeptum® GO base/nut/locking tool 5-port TC50.5	1	EAT52/5-3D0
NovaSeptum® GO base/nut/locking tool 9-port TC64	1	EAT92/6-3D0

## To Place and Order or Receive Technical Assistance

Please visit  
[EMDMillipore.com/contactPS](https://www.emdmillipore.com/contactPS)

For additional information, please visit  
[EMDMillipore.com](https://www.emdmillipore.com)

MilliporeSigma  
 400 Summit Drive  
 Burlington, MA 01803

