

Product Information

Anti-LRP1 (N-terminal)

produced in rabbit, affinity isolated antibody

Product Number **L2295**

Product Description

Anti-LRP1 (N-terminal) is produced in rabbit using as the immunogen a synthetic peptide corresponding to a sequence at the N-terminal of human LRP1 (GenelD: 4035), conjugated to KLH. The corresponding sequence is identical in mouse, rat, dog, and monkey. The antibody is affinity-purified using the immunizing peptide immobilized on agarose.

Anti-LRP1 (N-terminal) recognizes human, mouse, and rat LRP1 (not tested in other species). The antibody may be used in various immunochemical techniques including immunoblotting (~500 kDa) and immunofluorescence. Detection of the LRP1 band by immunoblotting is specifically inhibited by the immunizing peptide.

LDL receptor-related protein 1 (LRP1), also known as α -2-macroglobulin receptor, is a large endocytic receptor widely expressed on surface and intracellular membranes of many cells. LRP1 is a member of the LDL receptor family, which is involved in several biological processes. LRP1 is synthesized in the endoplasmic reticulum as a single-chain 600 kDa type I transmembrane glycosylated precursor that is cleaved subsequently in the Golgi complex into two subunits of ~515 kDa and 85 kDa. The 515 kDa N-terminal subunit remains attached to the membrane through noncovalent association with the smaller 85 kDa C-terminal subunit, which contains the transmembrane and cytoplasmic domains.

LRP1 expression is essential for early embryonic development. LRP1 functions in lipoprotein metabolism, proteinase regulation, activation of lysosomal enzymes, cellular entry of viruses and toxins, cell signaling pathways, cell migration, and neurodevelopment. LRP1 recognizes at least 30 different ligands including lipoproteins, proteinases, proteinase-inhibitor complexes, ECM proteins, bacterial toxins, viruses, and various intracellular proteins.¹⁻⁵

Reagent

Supplied as a solution in 0.01 M phosphate buffered saline, pH 7.4, containing 15 mM sodium azide.

Antibody concentration: ~1.0 mg/mL

Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

Storage/Stability

Store at -20 °C. For continuous use, the product may be stored at 2-8 °C for up to one month. For extended storage freeze in working aliquots at -20 °C. Repeated freezing and thawing is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use. Working dilution samples should be discarded if not used within 12 hours.

Product Profile

Immunoblotting: a working antibody concentration of 1-2 μ g/mL is recommended using a whole extract of human U87 cells; a working antibody concentration of 2-4 μ g/mL is recommended using a whole extract of mouse C2C12 cells.

Immunofluorescence: A working antibody concentration of 2-5 μ g/mL is recommended using rat NRK cells.

Note: In order to obtain best results in various techniques and preparations, it is recommended to determine optimal working dilutions by titration

References

1. Strickland, D.K. et al., *J. Biol. Chem.*, **265**, 17401-17404 (1990).
2. Herz, J. et al., *EMBO J.*, **9**, 1769-1776 (1990).
3. Herz, J., and Strickland, D.K., *J. Clin. Invest.*, **108**, 779-784 (2001).
4. May, P. et al., *Ann. Med.*, **39**, 219-228 (2007).
5. Lillis, A.P. et al., *Physiol. Rev.*, **88**, 887-918 (2008).

VS,ST,TD,KAA,PHC,MAM 04/19-1