

Product Information

Tumor Necrosis Factor- α human recombinant, expressed in HEK 293 cells suitable for cell culture

Product Number **H8916**
Storage Temperature $-20\text{ }^{\circ}\text{C}$

Synonyms: Cachectin, TNF- α , TNFA

Product Description

Recombinant human Tumor Necrosis Factor α (TNF- α) is expressed in human HEK 293 cells with a calculated molecular mass of 17 kDa (monomer). It has been shown to be predominantly a glycosylated, non-covalently linked homotrimer with a molecular mass of 51 kDa (gel filtration). This protein is manufactured in human cells, with no serum. The human cells expression system allows human-like glycosylation and folding, and often supports higher specific activity of the protein. The protein is produced with no artificial tags and no carrier proteins.

TNF- α is a protein secreted by lipopolysaccharide stimulated macrophages and causes tumor necrosis *in vivo* when injected into tumor bearing mice.¹ TNF- α is believed to mediate pathogenic shock and tissue injury associated with endotoxemia.² TNF- α is closely related to the 25 kDa protein Tumor Necrosis Factor- β (lymphotoxin), sharing the same receptors and cellular actions.³ TNF- α causes cytolysis or cytoostasis of certain transformed cells,^{4,5} being synergistic with γ -interferon in its cytotoxicity.⁶ Although it has little effect on many cultured normal human cells,⁵ TNF- α appears to be directly toxic to vascular endothelial cells.⁷

This product is lyophilized from a solution containing phosphate buffered saline (PBS), pH 7.4, with no carrier proteins. It is aseptically filled.

The biological activity of recombinant human TNF- α was tested in culture by measuring its ability to stimulate cytotoxicity of the TNF- α sensitive cell line L-929 in the presence of actinomycin D.

EC₅₀: $\leq 1.0\text{ ng/mL}$

The EC₅₀ is defined as the effective concentration of TNF- α that elicits a 50% decrease in cell growth in a cell-based bioassay.

Purity: $\geq 95.0\%$ (SDS-PAGE)

Endotoxin: $\leq 1.00\text{ EU}/\mu\text{g}$ TNF- α (LAL)

Uniprot: P01375

Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

Preparation Instructions

Briefly centrifuge the vial before opening. Reconstitute in water to a concentration of 0.1 mg/mL. Do not vortex. This solution can be stored at $2\text{--}8\text{ }^{\circ}\text{C}$ for up to 1 week. For extended storage, it is recommended to store in working aliquots at $-20\text{ }^{\circ}\text{C}$.

Storage/Stability

Store the lyophilized product at $-20\text{ }^{\circ}\text{C}$. The product is stable for at least 2 years as supplied.

References

1. Carswell, E.A., et al., Proc. Natl. Sci. USA, **72**, 3666 (1975).
2. Tracey, K.J., et al., Science, **234**, 470 (1986).
3. Hass, P.E., et al., J. Biol. Chem., **260**, 12213 (1985).
4. Granger, G.A., et al., J. Clin. Immunol., **5**, 217 (1985).
5. Helson, L., et al., Nature, **258**, 731 (1975).
6. Williamson, B D., et al., Proc. Natl. Acad. Sci. USA, **80**, 5397 (1983).
7. Sato, N., et al., J. Natl. Cancer Inst., **76**, 1113 (1986).

PCG,GS,JF,MAM 07/19-1